









A 1025 CGA 580
61"
Leased Tank


T
7.68m3





ACETYLENE CGA 510 CGA 520 CGA 200				
47"	38"	27"	22"	15"
Leased Tank	Leased Tank	Leased Tank	Customer Owned Tank	Customer Owned Tank
				
A390	CWS	CWQ	B	MC
Average Volume	Average Volume	Average Volume		
10.12m3	3.51m3	2.08m3	1.11m3	.28m3




ARGON CGA 580		
61"	52"	36"
Leased Tank	Leased Tank	Leased Tank
		
T	S	Q
9.29m3	4.26m3	2.3m3

BREATHING AIR CGA 346
57"
Leased Tank

K
6.43m3




C-15 CGA 580
61"
Leased Tank

T
10.51m3


C-25 AUTOWELD CGA 580			
61"	52"	36"	27"
Leased Tank	Leased Tank	Leased Tank	Customer Owned Tank
			
T	S	Q	LD
10.60m3	4.80m3	2.63m3	1.93m3







CARBON DIOXIDE CGA 320			
56"	56"	36"	18"
Leased Tank	Leased Tank	Leased Tank	Customer Owned Tank
			
T	K	Q	R
29.0KG	22.7KG	9.07KG	2.27KG
65LBs	50LBs	20LBs	5LBs





COMPRESSED AIR CGA 346
57"
Leased Tank



K
6.43m3






HELIUM ULTRA LIFT CGA 580		
61"	52"	36"
Leased Tank	Leased Tank	Leased Tank
		
T	S	Q
8.07m3	3.74m3	2.02m3

MIG MIX GOLD CGA 580
60"
Leased Tank

HC
14.36m3

MEDICAL OXYGEN CGA 540 CGA 870					
56"	29"	20"	29"	20"	29"
Leased Tank	Leased Tank	Leased Tank	Leased Tank	Leased Tank	Leased Tank
					
K	MBE	MD	MBE	MD	XES
6.9m3	.69m3	.42m3	.69m3	.42m3	.69m3
6900L	690L	420L	690L	420L	690L

OXYGEN CGA 540				
57"	52"	36"	27"	18"
Leased Tank	Leased Tank	Leased Tank	Customer Owned Tank	Customer Owned Tank
				
K	S	Q	LD	R
6.9m3	4.27m3	2.3m3	1.61m3	.58m3

HYDROGEN CGA 350	
57"	36"
Leased Tank	Leased Tank
	
K	Q
5.3m3	1.72m3

NITROGEN CGA 580				
61"	52"	36"	37"	18"
Leased Tank	Leased Tank	Leased Tank	Leased Tank	Customer Owned Tank
				
T	S	Q	LL	R
8.42m3	3.92m3	2.12m3	2.27m3	.52m3



Cylinder Safety Tips

- Always have the cylinder cap in place when the cylinder is not in use or in transit.
- Never place acetylene or propane cylinder in the trunk of a vehicle.
- Always store acetylene and propane in an open, well ventilated area.
- Always secure cylinders whether in use, storage or transportation.
- Always turn cylinders completely off when you have finished using them.